

Technical data sheet

Service pole, type ISSRM45

Item number: 6290087



ISS aluminium service pole with a 45 mm system opening.

Set consists of:

1 one-compartment pole with clamping fastening

Total length: 3,315 mm–3,480 mm

1 ceiling attachment with clamping device

1 aluminium cover

Length: 3,000 mm

The design of this ISS service pole is based on an extremely slender, round aluminium profile, which has a smooth cover of the Rapid 45 device installation trunking series as its front side. The 45 mm system opening is suitable for direct acceptance of Modul 45® switching and connection devices.



Alu Aluminium

EL Anodised

Master data

Item number	6290087
Type	ISSRM45EL
Description 1	Service pole
Description 2	floor/ceiling
Manufacturer	OBO
Dimension	3000x70x59
Colour	aluminium
Material	Aluminium
Surface	Anodised
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	510 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	109,0436 kg CO2e / 1 Piece


Technical data sheet

Service pole, type ISSRM45

Item number: 6290087



Dimensions



Length	3,000 mm
Width	70 mm
Height	59 mm

Technical data

Number of usable covers	1
Number of compartments	1 St.
Version for	Single-sided
Fastening type	Tension
Floor mounting	yes
Ceiling mounting	yes
Continuous profile	yes
Halogen-free	yes
Height compensation, max.	480 mm
Height compensation, min.	315 mm
Cable entry	Top
Cover width	45 mm
Changes according to location	no
ROHS-conformant	yes
Pole shape	Round
Pole height, max.	3480 mm
Pole height, min.	3315 mm
Adjustable	yes
Pre-wired	no