

Technical data sheet

Head plate, variable A2

Item number: 6348884



Head plate for the installation on US 3 supports and profile rails, type AML3518/AMS3518 and CML3518/CMS3518.

The variable head plate can be mounted to fixed lengths of the U support, type US 3, or profile rails, type AML3518/AMS3518 and CML3518/CMS3518. The maximum angle adjustment is 20° on one side.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6348884
Type	KU 3 V A2
Description 1	Head plate
Description 2	for US 3 and 3518, variable
Manufacturer	OBO
Dimension	140x120x40
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	40 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	3,1357 kg CO2e / 1 Piece


Technical data sheet

Head plate, variable A2

Item number: 6348884



Dimensions



Length	140 mm
Width	40 mm
Height	120 mm

Technical data

Version for	Screw head plate
Maintain electrical functions	no
Suitable for ceiling fastening	yes
Suitable for panel fastening	no
Suitable for profile shapes	U profile
ROHS-conformant	yes
Rustproof steel, pickled	no
Angle range, max.	90 mm
Angle range, min.	90 mm