


# Technical data sheet

## MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 6349463



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



|    |                    |
|----|--------------------|
| St | Steel              |
| FT | Hot-dip galvanised |

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 6349463                  |
| Type                               | MS5030RP0380FT           |
| Description 1                      | Profile rail             |
| Description 2                      | perforated, slot 22mm    |
| Manufacturer                       | OBO                      |
| Dimension                          | 380x50x30                |
| Material                           | Steel                    |
| Surface                            | Hot-dip galvanised       |
| Surface standard                   | DIN EN ISO 1461          |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 119 kg                   |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 2,4158 kg CO2e / 1 Piece |


# Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 6349463



## Dimensions



|             |        |
|-------------|--------|
| Length      | 380 mm |
| Width       | 50 mm  |
| Height      | 30 mm  |
| Dimension L | 380 mm |

## Technical data

|                             |                       |
|-----------------------------|-----------------------|
| Breakable                   | no                    |
| Type of perforation         | Perforated back       |
| Version for                 | Single profile        |
| Drill hole spacing, centre  | 70 mm                 |
| Material thickness          | 3 mm                  |
| With perforation            | yes                   |
| With tothing                | no                    |
| Profile shape               | C profile             |
| Slot width                  | 22 mm                 |
| Static value A              | 3.39 cm <sup>2</sup>  |
| Static value I <sub>y</sub> | 3.99 cm <sup>4</sup>  |
| Static value I <sub>z</sub> | 13.11 cm <sup>4</sup> |
| Static value W <sub>y</sub> | 3.95 cm <sup>3</sup>  |
| Static value W <sub>z</sub> | 6.38 cm <sup>3</sup>  |