

Technical data sheet

Truss-head bolt with nut and washer A4

Item number: 6406564



Truss-head bolt with square neck including hexagonal nut and washer.
For example, for use in longitudinal hole 7 x 20 mm or 7 x 32 mm.




A4 Stainless steel

Master data

Item number	6406564
Type	FRS 6x12 A4
Description 1	Truss-head bolt
Description 2	with washer and nut
Manufacturer	OBO
Dimension	M6x12
Colour	stainless steel
Material	Stainless steel 1.4401
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.82 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0396 kg CO2e / 1 Piece

Dimensions



Length	12 mm
Dimension D	13.5 mm
Dimension d	6 mm
Dimension L	12 mm

Technical data sheet

Truss-head bolt with nut and washer A4

Item number: 6406564



Technical data

Resistance grade	A4-70
Thread metric	6
Thread type	Metric
Head shape	Flat round head with square
With flange	no
With nut	yes
With washer	yes
ROHS-conformant	yes
WAF	10
Screw system	Miscellaneous
Self-locking	no
Full thread	yes
Left thread	no