

Technical data sheet

Truss-head bolt with nut and washer A2

Item number: 6406602



Truss-head bolt with square neck including hexagonal nut and washer.
The truss-head bolt is used in conjunction with the clamp, type GKS 34 and the connector, type GSV 34.




A2 Stainless steel

Master data

Item number	6406602
Type	FRS 6x20 A2
Description 1	Truss-head bolt
Description 2	with washer and nut
Manufacturer	OBO
Dimension	M6x20
Colour	stainless steel
Material	Stainless steel 1.4301
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.942 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,047 kg CO2e / 1 Piece

Dimensions



Length	20 mm
Dimension D	13.5 mm
Dimension d	6 mm
Dimension L	20 mm

Technical data sheet

Truss-head bolt with nut and washer A2

Item number: 6406602



Technical data

Resistance grade	A2-70
Thread metric	6
Thread type	Metric
Head shape	Flat round head with square
With flange	no
With nut	yes
With washer	yes
ROHS-conformant	yes
WAF	10
Screw system	Miscellaneous
Self-locking	no
Full thread	yes
Left thread	no