


# Technical data sheet

## Adjustable bend element, vertical 85 FS

Item number: 7005482



Adjustable vertical bend element, for all cable tray types with a side height of 85 mm.  
RGV 85 adjustable connectors should be ordered separately and in the appropriate quantity.



St

Steel

FS

Strip galvanised

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 7005482                  |
| Type                               | RGBEV 820 FS             |
| Description 1                      | Adjustable bend element  |
| Description 2                      | vertical                 |
| Manufacturer                       | OBO                      |
| Dimension                          | 85x200                   |
| Colour                             | zinc                     |
| Material                           | Steel                    |
| Surface                            | Strip galvanised         |
| Surface standard                   | DIN EN 10346             |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 91.9 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 3,4524 kg CO2e / 1 Piece |


# Technical data sheet

## Adjustable bend element, vertical 85 FS

Item number: 7005482



### Dimensions



|                 |        |
|-----------------|--------|
| Width           | 200 mm |
| Width           | 8 in   |
| Height          | 85 mm  |
| Height          | 3 in   |
| Plate thickness | 1 mm   |
| Dimension B     | 200 mm |

### Technical data

|                                         |                          |
|-----------------------------------------|--------------------------|
| Bend (angle)                            | Adjustable               |
| Connector version                       | Without connectors       |
| Type                                    | Adjustable bend element  |
| Maintain electrical functions           | no                       |
| Mounting perforation in base            | no                       |
| NATO hole pattern                       | no                       |
| Change of direction                     | Vertical, rising/falling |
| ROHS-conformant                         | yes                      |
| Rustproof steel, pickled                | no                       |
| Side perforation                        | no                       |
| Wide-span version                       | no                       |
| Type of connector, cable support system | Screwed                  |