

Technical data sheet

90° adjustable bend, vertical 60 FS

Item number: 7006330



90° adjustable vertical bend, for all cable tray types with a side height of 60 mm. The bend is shipped in an unmounted state. No additional fastening materials are required.



St

Steel

FS

Strip galvanised

Master data

Item number	7006330
Type	RGBV 615 FS
Description 1	Adjustable bend
Description 2	vertical
Manufacturer	OBO
Dimension	60x150
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	200 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	6,6665 kg CO2e / 1 Piece

Technical data sheet

90° adjustable bend, vertical 60 FS

Item number: 7006330



Dimensions

Width	150 mm
Width	6 in
Height	60 mm
Height	2 in
Plate thickness	1 mm
Dimension R	400 mm

Technical data

Bend (angle)	90°
Connector version	Supplied connectors
Type	Adjustable bend_complete
Maintain electrical functions	no
Mounting perforation in base	no
NATO hole pattern	no
Change of direction	Vertical, rising/falling
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	no
Wide-span version	no
Type of connector, cable support system	Screwed