

Technical data sheet

90° bend 35 FT

Item number: 7124410



90° bend for horizontal routing of cable trays, type RKS 305.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	7124410
Type	RB 90 305 FT
Description 1	90° bend
Description 2	horizontal
Manufacturer	OBO
Dimension	35x50
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	32.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,1893 kg CO2e / 1 Piece


Technical data sheet

90° bend 35 FT

Item number: 7124410



Dimensions



Width	50 mm
Height	35 mm
Height	1 in
Dimension B	50 mm

Technical data

Bend (angle)	90°
Connector version	Supplied connectors
Type	Bend, rigid
Maintain electrical functions	no
Mounting perforation in base	no
NATO hole pattern	no
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	no
Wide-span version	no
Type of connector, cable support system	Screwed