

Technical data sheet

Cover for 90° vertical bend, rising, A2

Item number: 7130913



Cover for all rising vertical bends.

The fastening is guaranteed by the overlap of the cable tray covers. The cover can also be fastened using cover clamps.



A2 Stainless steel

2B Bright, treated

Master data

Item number	7130913
Type	DBV 500 S A2
Description 1	Cover for 90° vertical bend
Description 2	rising
Manufacturer	OBO
Dimension	B500mm
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	86 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	10,4977 kg CO2e / 1 Piece


Technical data sheet

Cover for 90° vertical bend, rising, A2

Item number: 7130913



Dimensions



Width	500 mm
Width	20 in
Plate thickness	0.03 in
Plate thickness	0.75 mm
Dimension B	500 mm

Technical data

Bend (angle)	90°
Fastening type	Cover clamp
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Change of direction	Vertical rising
ROHS-conformant	yes
Rustproof steel, pickled	no
Hinged	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C