

Technical data sheet

90° bend VS 60 A2

Item number: 7160046



90° bend, horizontal, for cable ladders with VS rungs and a side height of 60 mm. Connectors should be ordered separately and in the appropriate quantity.




A2 Stainless steel

2B Bright, treated

Master data

Item number	7160046
Type	LBI 90 620 VS A2
Description 1	90° bend
Description 2	for cable ladder with VS rung
Manufacturer	OBO
Dimension	60x200
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	358 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	18,7251 kg CO2e / 1 Piece

Dimensions



Width	200 mm
Height	60 mm

Technical data sheet

90° bend VS 60 A2

Item number: 7160046



Technical data

Bend (angle)	90°
Version of the rungs	Profile unperforated
Side rail version	Flat profile
Maintain electrical functions	no
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Hinged	no
Side perforation	no
Wide-span version	no