

Technical data sheet

Head plate, longitudinal SOMY

Item number: 7193017



Head plate for mounting on IS 8 support. The cable trays and ladders run in a longitudinal direction.
The head plate is mounted to fixed lengths of the U support, type IS 8, using truss-head bolts, type FRS M10 x 25. The length of the support is limited to max. 2,000 mm. The surface coating is a coating created in a single-dip method with extra-high zinc thicknesses.



St	Steel
FT SO	Hot-dip galvanised 85 µm

Master data

Item number	7193017
Type	KI 8 FT SO
Description 1	Head plate
Description 2	for IS 8 support
Manufacturer	OBO
Dimension	200mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	156 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	4,2513 kg CO2e / 1 Piece


Technical data sheet

Head plate, longitudinal SOMY

Item number: 7193017



Dimensions



Length	200 mm
Width	100 mm
Height	150 mm

Technical data

Version for	Screw head plate
Suitable for ceiling fastening	yes
Suitable for panel fastening	no
Suitable for profile shapes	I profile
ROHS-conformant	yes
Rustproof steel, pickled	no
Angle range, max.	90 mm
Angle range, min.	90 mm