

Technical data sheet

US 7 support FT SOMY

Item number: 7193632



U support in fixed lengths. Dimensions 70 x 50 mm.

The surface coating is a coating created in a single-dip method with extra-high zinc thicknesses. For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 61.



St

Steel



Hot-dip galvanised 85 µm

Master data

Item number	7193632
Type	US 7 200 FT SO
Description 1	U support
Description 2	3-sided perforated
Manufacturer	OBO
Dimension	70x50x2000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	814.3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	22,658 kg CO2e / 1 Piece


Technical data sheet

US 7 support FT SOMY


Item number: 7193632



Dimensions



Dimension	70 x 50 x 4
Length	2,000 mm
Width	70 mm
Height	50 mm



Technical data sheet

US 7 support FT SOMY

Item number: 7193632



Technical data

Breakable	no
Type of perforation	3 sides perforated
Version for	Single profile
Maintain electrical functions	no
Material thickness	4 mm
With toothing	no
Profile shape	U profile
ROHS-conformant	yes
Static value A	4.59 cm ²
Static value I _y	13.79 cm ⁴
Static value I _z	36.84 cm ⁴
Static value W _y	4.11 cm ³
Static value W _z	10.53 cm ³