


# Technical data sheet

## Cable tray SKSU 110 FT SOMY

Item number: 7196014



SKS 110 = heavy-duty cable tray system, unperforated, with 110 mm side height. The cable tray has connector perforations on both sides. Straight connectors should be ordered separately and in the appropriate quantity. Magnetic shield insulation without cover 20 dB, with cover 50 dB.



St

Steel

FT  
SO

Hot-dip galvanised 85 µm

### Master data

|                                    |                               |
|------------------------------------|-------------------------------|
| Item number                        | 7196014                       |
| Type                               | SKSU 140 FT SO                |
| Description 1                      | Cable tray SKSU               |
| Description 2                      | unperforated, connector holes |
| Manufacturer                       | OBO                           |
| Dimension                          | 110x400x3000                  |
| Colour                             | zinc                          |
| Material                           | Steel                         |
| Surface                            | Hot-dip galvanised 85 µm      |
| Surface standard                   | DIN EN ISO 1461               |
| Smallest sales unit                | 3                             |
| Unit of quantity                   | Metre                         |
| Weight                             | 822.7 kg                      |
| Weight unit                        | kg/100 m                      |
| CO2 Footprint (GWP) Cradle-to-Gate | 17,4688 kg CO2e / 1 Meter     |


# Technical data sheet

## Cable tray SKSU 110 FT SOMY

Item number: 7196014



### Dimensions



|                 |          |
|-----------------|----------|
| Length          | 3,000 mm |
| Width           | 400 mm   |
| Height          | 110 mm   |
| Plate thickness | 1.5 mm   |
| Dimension B     | 400 mm   |



### Technical data

|                                         |                     |
|-----------------------------------------|---------------------|
| Connector version                       | Without connectors  |
| Mounting system fastening type          | Floor Ceiling Wall  |
| Walkable                                | no                  |
| Maintain electrical functions           | no                  |
| With cover                              | no                  |
| Mounting perforation in base            | no                  |
| NATO hole pattern                       | no                  |
| Usable cross-section                    | 438 cm <sup>2</sup> |
| ROHS-conformant                         | yes                 |
| Rustproof steel, pickled                | no                  |
| Side perforation                        | no                  |
| Wide-span version                       | no                  |
| Load test type according to IEC 61537   | Type II             |
| Type of connector, cable support system | Screwed             |

# Technical data sheet


## Cable tray SKSU 110 FT SOMY

Item number: 7196014



### Loads

|                                   |           |
|-----------------------------------|-----------|
| Insertable support spacings, min. | 4 m       |
| Support spacing 1.5 m             | 3 kN/m    |
| Support spacing 2.0 m             | 2.4 kN/m  |
| Support spacing 2.5 m             | 1.76 kN/m |
| Support spacing 3.0 m             | 1.2 kN/m  |
| Support spacing 3.5 m             | 0.84 kN/m |
| Support spacing 4.0 m             | 0.8 kN/m  |



### Load diagram, cable tray, type SKSU 110

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width