


Technical data sheet

Strain relief on three sides, with mineral wool, internal height 115 mm

Item number: 7215702



Strain relief as an effective support measure for vertical cable routing, according to DIN 4102 Part 12, approved for all cable types and all vertical routing systems. Maintenance of electrical function classes E30 to E90. Housing including mineral fibre panels, fastening material, ASX fire protection coating in cartridge and identification plate.

Calcium silicate

Master data

Item number	7215702
Type	ZSE90-25-11
Description 1	Strain relief
Description 2	for vertical cable routing
Manufacturer	OBO
Dimension	340x160x140
Colour	Cream; RAL 9001
Material	Calcium silicate
Smallest sales unit	1
Unit of quantity	Piece
Weight	376 kg
Weight unit	kg/100 pc.


Technical data sheet

Strain relief on three sides, with mineral wool, internal height 115 mm

Item number: 7215702



Dimensions



Length	140 mm
Width	340 mm
Height	160 mm
Dimension B	340 mm
Dimension b	250 mm
Dimension H	140 mm
Dimension t	160 mm
Dimension t	115 mm

Technical data

Fire protection version	Soft insulation
Shape	Rectangular
ROHS-conformant	yes
Accessories required	no