


Technical data sheet

Strain relief on three sides, empty housing, internal height
175 mm

Item number: 7215772



Strain relief as an effective support measure for vertical cable routing, according to DIN 4102 Part 12. Approved for all cable types and all vertical routing systems, which are mounted directly on solid walls. Maintenance of electrical function classes E30 to E90. Empty housing for individual filling with the PYROSIT® NG fire protection foam and/or PYROPLUG® Block insulation systems, incl. mounting set and labelling panel.

Calcium silicate

Master data

Item number	7215772
Type	ZSE90-55-17 L
Description 1	Strain relief
Description 2	for vertical cable routing
Manufacturer	OBO
Dimension	600x200x200
Colour	Cream; RAL 9001
Material	Calcium silicate
Smallest sales unit	1
Unit of quantity	Piece
Weight	530 kg
Weight unit	kg/100 pc.


Technical data sheet

Strain relief on three sides, empty housing, internal height
175 mm

Item number: 7215772



Dimensions



Length	200 mm
Width	600 mm
Height	200 mm
Dimension B	600 mm
Dimension b	550 mm
Dimension H	200 mm
Dimension t	200 mm
Dimension t	175 mm

Technical data

Shape	Rectangular
ROHS-conformant	yes