

Technical data sheet

Flat angle, duct height 120 mm, FS

Item number: 7218071



45° flat angle with intumescent fire protection mesh for PYROLINE® Rapid PLM installation duct. Suitable for direct wall and ceiling mounting, mounting below system floors and mounting on support systems. Tool-free joint mounting with PLM SI joint connector. The cover is snapped on without tools, allowing rapid inspection and retroassignment. The cover overhang allows offset cover mounting for continuous equipotential bonding of the entire duct section. No maintenance of electrical functionality according to DIN 4102 Part 12!



St Steel

FS Strip galvanised

Master data

Item number	7218071
Type	PLM FA45 1220 FS
Description 1	Flat angle
Description 2	with fire protection mesh
Manufacturer	OBO
Dimension	340x490x120
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	220 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	6,9563 kg CO2e / 1 Piece


Technical data sheet

Flat angle, duct height 120 mm, FS

Item number: 7218071



Dimensions



Dimension L	487 mm
Dimension L2	183 mm
Dimension W	200 mm

Technical data

Number of flammable sides	4
Cover fastening	Miscellaneous
Classification EI – installation duct	90
With perforation	yes
Usable cross-section	18500 mm ²
ROHS-conformant	yes
Partitions possible	no
Jacketing	Steel
Angle of the bend	45 °