


Technical data sheet

T branch piece, duct height 120 mm, pure white

Item number: 7218084



Tee with intumescent fire protection mesh for PYROLINE® Rapid PLM installation duct. Suitable for direct wall and ceiling mounting, mounting below system floors and on support systems. Tool-free joint mounting with PLM SI joint connector. The cover is snapped on without tools, allowing rapid inspection and retroassignment. The cover overhang allows offset cover mounting for continuous equipotential bonding of the entire duct section.



St Steel

P Powder-coated

Master data

Item number	7218084
Type	PLM TB 1220 RW
Description 1	T-branch
Description 2	with fire protection mesh
Manufacturer	OBO
Dimension	600x400x120
Colour	Pure white; RAL 9010
Material	Steel
Surface	Powder-coated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	350 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	13,1577 kg CO2e / 1 Piece


Technical data sheet

T branch piece, duct height 120 mm, pure white

Item number: 7218084



Dimensions



Dimension A	400 mm
Dimension B	200 mm
Dimension H	120 mm
Dimension t	600 mm

Technical data

Number of flammable sides	4
Classification EI - installation duct	90
With perforation	yes
Usable cross-section	18500 mm ²
ROHS-conformant	yes
Partitions possible	yes
Jacketing	Steel