

Technical data sheet

UDHOME-ONE floor socket, with floor covering recess, BS
socket, stainless steel
Item number: 7368307



Square floor socket for use in dry-care systems and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M20/M25). Cover adjustable to top edge of floor covering using four height-adjustment supports. The minimum installation depth is 85 mm, the height adjustment range +20 mm. Frame and cover made of stainless steel and visible in the floor covering. Cover with floor covering recess. The delivery includes a switched BS socket.



A2 Stainless steel

Master data


Item number	7368307
Type	UDHOME-ONE V15BS
Description 1	Floor socket
Description 2	BS socket, 15mm floor recess
Manufacturer	OBO
Dimension	140x140x85
Material	Stainless steel
Smallest sales unit	1
Unit of quantity	Piece
Weight	211 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	11,1641 kg CO2e / 1 Piece

Technical data sheet


UDHOME-ONE floor socket, with floor covering recess, BS socket, stainless steel
Item number: 7368307



Dimensions



Length	140 mm
Width	140 mm
Height	85 mm



Technical data

Number of sockets according to the British standard	1
Cable outlet version	Swivellable cord outlet
Equipment	Single BS socket
Floor covering protection frame	no
Floor care	Dry
Cover version	Floor covering recess
Seal installation option	no
Application when used	6.101.1 Dry floor care
Application when unused	6.101.1 Dry floor care
Floor height, max.	105 mm
Floor height, min.	85 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	no
With floor covering recess	yes
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no

Technical data sheet

UDHOME-ONE floor socket, with floor covering recess, BS
socket, stainless steel

Item number: 7368307



Technical data

Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Opening mechanism	Handle
Floor covering thickness	15 mm