


Technical data sheet

UDHOME-ONE floor socket, with floor covering recess, BS
socket, brass

Item number: 7368310



Square floor socket for use in dry-care systems and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M20/M25). Cover adjustable to top edge of floor covering using four height-adjustment supports. The minimum installation depth is 85 mm, the height adjustment range +20 mm. Frame and cover made of brass and visible in the floor covering. Cover with floor covering recess. The delivery includes a switched BS socket.



Brass

Master data

Item number	7368310
Type	UDHOME-ONE M15BS
Description 1	Floor socket
Description 2	BS socket, 15mm floor recess
Manufacturer	OBO
Dimension	140x140x85
Material	Brass
Smallest sales unit	1
Unit of quantity	Piece
Weight	227 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	9,9289 kg CO2e / 1 Piece


Technical data sheet

UDHOME-ONE floor socket, with floor covering recess, BS socket, brass


Item number: 7368310



Dimensions



Length	140 mm
Width	140 mm
Height	85 mm



Technical data

Number of sockets according to the British standard	1
Cable outlet version	Swivellable cord outlet
Equipment	Single BS socket
Floor covering protection frame	no
Floor care	Dry
Cover version	Floor covering recess
Seal installation option	no
Application when used	6.101.1 Dry floor care
Application when unused	6.101.1 Dry floor care
Floor height, max.	105 mm
Floor height, min.	85 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	no
With floor covering recess	yes
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no

Technical data sheet

UDHOME-ONE floor socket, with floor covering recess, BS
socket, brass

Item number: 7368310



Technical data

Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Opening mechanism	Handle
Floor covering thickness	15 mm