

Technical data sheet

Floor socket UDHOME-ONE, with brush outlet, without floor covering recess, unequipped, stainless steel
Item number: 7368356



Square floor socket for the use in dry-cleaned system and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M20/M25). Cover adjustable to the upper edge of the floor covering with 4 height-adjustment supports. The minimum installation depth is 75 mm, the height-adjustment range is +30 mm. Frame and stainless steel cover visible in the floor covering. Cover with decorative plate and brush outlet for routing cables. Empty housing for one Modul 45® installation device and one data socket. Closed with a blind plate when delivered.



A2 Stainless steel

2B Bright, treated

Master data

Item number	7368356
Type	UDHOME-ONE BN
Description 1	Floor socket
Description 2	unequipped, with brush outlet
Manufacturer	OBO
Dimension	140x140x75
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	200 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	11,2094 kg CO2e / 1 Piece

Technical data sheet


Floor socket UDHOME-ONE, with brush outlet, without floor covering recess, unequipped, stainless steel
Item number: 7368356



Dimensions



Length	140 mm
Width	140 mm
Height	75 mm
Dimension h	75 mm



Technical data

Number of installable devices	2
No. of entries	6
Number of mounting boxes	0
Number of SCHUKO sockets	0
Number of sockets according to the British standard	0
Cover version	Square
Cable outlet version	Brush bar
Equipment	Empty housing
Floor covering protection frame	no
Floor care	Dry
Cover version	Decorative plate
Seal installation option	no
Application when used	6.101.1 Dry floor care
Application when unused	6.101.1 Dry floor care
Screed height, max.	105 mm
Screed height, min.	75 mm
Floor height, max.	105 mm
Floor height, min.	75 mm
Suitable for outdoor use	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	no
Length of external dimensions	140 mm
Length of installation dimensions	144 mm
With floor covering recess	no

Technical data sheet

Floor socket UDHOME-ONE, with brush outlet, without floor covering recess, unequipped, stainless steel
Item number: 7368356



Technical data

Nominal size for device installation units	2
Height-adjustment range, max.	105 mm
Height-adjustment range, min.	75 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no
Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE