


Technical data sheet

Floor socket UDHOME-ONE, with brush outlet, with floor covering recess, unequipped, stainless steel

Item number: 7368357



Square floor socket for use in dry-cleaned system and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M20/M25). Cover adjustable to the upper edge of the floor covering with 4 height-adjustment supports. The minimum installation depth is 75 mm, the height-adjustment range is +30 mm. Frame and stainless steel cover visible in the floor covering. Cover with floor covering recess and brush outlet for routing cables. Empty housing for one Modul 45® installation device and one data socket. The data technology support for the data socket is to be ordered separately. The space is closed with a blind plate when delivered.



A2 Stainless steel

2B Bright, treated

Master data

Item number	7368357
Type	UDHOME-ONE BN15
Description 1	Floor socket
Description 2	unequipped, with brush outlet
Manufacturer	OBO
Dimension	140x140x75
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	200 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	11,0264 kg CO2e / 1 Piece


Technical data sheet

Floor socket UDHOME-ONE, with brush outlet, with floor covering recess, unequipped, stainless steel

Item number: 7368357



Dimensions



Length	140 mm
Width	140 mm
Height	75 mm
Dimension h	75 mm

Technical data

Number of installable devices	2
No. of entries	6
Number of socket outlets with protective contact CEE 7/3 (type F)	0
Number of sockets according to the British standard	0
Cover version	Square
Cable outlet version	Brush bar
Equipment	Empty housing
Floor covering protection frame	no
Floor care	Dry
Cover version	Floor covering recess
Seal installation option	no
Application when used	6.101.1 Dry floor care
Application when unused	6.101.1 Dry floor care
Screed height, max.	105 mm
Screed height, min.	75 mm
Floor height, max.	105 mm
Floor height, min.	75 mm
Suitable for outdoor use	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	no
Length of external dimensions	140 mm
Length of installation dimensions	144 mm

Technical data sheet

Floor socket UDHOME-ONE, with brush outlet, with floor covering recess, unequipped, stainless steel

Item number: 7368357



Technical data

With floor covering recess	yes
Nominal size for device installation units	2
Height-adjustment range, max.	105 mm
Height-adjustment range, min.	75 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no
Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE
Floor covering thickness	15 mm