

Technical data sheet

Underfloor duct, 2 pieces, 3-compartment, duct height
48 mm

Item number: 7400281



Underfloor trunking (2 piece) for routing cables in screed-covered underfloor systems, according to EN 50085-2-2. Removable and continuously lockable trunking cover. With separating retainers in the trunking base. Maximum load-bearing capacity to 1.5 kN.

The profiled side walls offer a locking mechanism to lock the duct cover onto the duct base. The stiffening beads in the duct cover serve to create stability.



St	Steel
FS	Strip galvanised

Master data

Item number	7400281
Type	S3 25048-2
Description 1	Underfloor duct, 2-part
Description 2	3 compartments
Manufacturer	OBO
Dimension	2000x250x48
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	453.8 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	10,0773 kg CO2e / 1 Meter


Technical data sheet

Underfloor duct, 2 pieces, 3-compartment, duct height
48 mm

Item number: 7400281



Dimensions



Length	2,000 mm
Width	250 mm
Height	48 mm
Dimension a	90 mm
Dimension b	70 mm
Dimension h	48 mm

Technical data

Number of fixed partitions	2
Number of compartments	3 St.
Mounting system fastening type	Floor
Floor plate	yes
Application area	Screed-covered
Decouplable	no
Trunking width, min.	250 mm
Duct height, min.	48 mm
Usable cross-section	10892 mm ²
Removable cover	yes
Cross-section, draw a	3854 mm ²
Cross-section, draw b	3184 mm ²
ROHS-conformant	yes
Vertical load, large area	to 1,500 N