


Technical data sheet

Underfloor duct, 2 pieces, 3-compartment, duct height
58 mm

Item number: 7400293



Underfloor trunking (2 piece) for routing cables in screed-covered underfloor systems, according to EN 50085-2-2. Removable and continuously lockable trunking cover. With separating retainers in the trunking base. Maximum load-bearing capacity to 1.5 kN. Only compatible with the UZD250-4/350-4. The profiled side walls offer a locking mechanism to lock the duct cover onto the duct base. The stiffening beads in the duct cover serve to create stability.



St	Steel
FS	Strip galvanised

Master data

Item number	7400293
Type	S3 35058-2
Description 1	Underfloor duct, 2-part
Description 2	3 compartments
Manufacturer	OBO
Dimension	2000x350x58
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	422.969 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	13,0595 kg CO2e / 1 Meter


Technical data sheet

Underfloor duct, 2 pieces, 3-compartment, duct height
58 mm

Item number: 7400293



Dimensions



Length	2,000 mm
Width	350 mm
Height	58 mm
Dimension a	120 mm
Dimension b	110 mm
Dimension h	58 mm

Technical data

Number of fixed partitions	2
Number of compartments	3 St.
Mounting system fastening type	Floor
Floor plate	yes
Application area	Screed-covered
Decouplable	no
Trunking width, min.	350 mm
Duct height, min.	58 mm
Usable cross-section	18794 mm ²
Removable cover	yes
Cross-section, draw a	6341 mm ²
Cross-section, draw b	6112 mm ²
ROHS-conformant	yes
Vertical load, large area	to 1,500 N