


Technical data sheet

Underfloor box UDS9 for PVC duct

Item number: 7400352



Underfloor outlet box with fixed, unchangeable 244 x 244 mm installation opening for an installation unit of nominal size 9. The mounting opening is created using the screed protection cover contained in the scope of supply. The underfloor box possesses installation openings for three single-compartment PVC ducts of nominal size 60 x 25 and 90 x 35 on all four sides. The box is principally suited for use in floor structures in cement screed with a structure height of up to 100 mm.



St Steel

FS Strip galvanised

Master data

Item number	7400352
Type	UDSPD 9035 9
Description 1	Underfloor box
Description 2	for GES9
Manufacturer	OBO
Dimension	308x308x92
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	225 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	8,5594 kg CO2e / 1 Piece


Technical data sheet

Underfloor box UDS9 for PVC duct

Item number: 7400352



Dimensions



Length	308 mm
Width	308 mm
Height	92 mm

Technical data

Floor plate	yes
Seal installation option	yes
Installation opening for flush-mount unit	Rectangular
Screed height, max.	100 mm
Screed height, min.	65 mm
Suitable for screed-covered underfloor ducts	yes
Trunking width, max.	90 mm
Trunking width, min.	60 mm
Trunking height, max.	35 mm
Duct height, min.	25 mm
Nominal size for device installation units	9
ROHS-conformant	yes