


Technical data sheet

UDS underfloor connection sockets

Item number: 7400417



Underfloor connection socket with fixed, unchangeable installation opening for an installation unit of nominal size 9. The mounting opening is created using the screed protection cover contained in the scope of supply. The underfloor socket possesses installation openings for 2 or 3-compartment underfloor ducts made of sheet steel on all four sides.



St	Steel
FS	Strip galvanised

Master data

Item number	7400417
Type	UDSSD 35048 9
Description 1	Underfloor box
Description 2	for GES9, trunking width 350
Manufacturer	OBO
Dimension	420x420x200
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	393 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	17,8959 kg CO2e / 1 Piece


Technical data sheet

UDS underfloor connection sockets

Item number: 7400417



Dimensions



Length	420 mm
Width	420 mm
Height	51 mm
Dimension A	420 mm
Dimension B	420 mm
Dimension b	244 mm
Dimension h	51 mm

Technical data

Expansion option	For installation of accessories
Installation opening for on-floor tank	no
Installation opening for flush-mount unit	Square
Screed height, max.	200 mm
Screed height, min.	90 mm
For pipe connection	no
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Suitable for underfloor ducts	yes
Trunking width, max.	350 mm
Trunking width, min.	190 mm
Trunking height, max.	48 mm
Duct height, min.	28 mm
Material thickness	1 mm
Minimum screed height	90
Nominal size for device installation units	9
ROHS-conformant	yes