

Technical data sheet

Vertical bend, three-compartment, height 28 mm

Item number: 7400657



Vertical bend, two-compartment, for vertical direction changes of screed-covered underfloor ducts (wall connections, supplies).



CR	St	Chloroprene rubber	Steel
FS		Strip galvanised	

Master data

Item number	7400657
Type	KV3 35028-2
Description 1	Vertical bend
Description 2	3 compartments for EÜK-2
Manufacturer	OBO
Dimension	430x177,7x177,7
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	127.02 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	4,5586 kg CO2e / 1 Piece


Technical data sheet

Vertical bend, three-compartment, height 28 mm

Item number: 7400657



Dimensions



Length	178 mm
Width	350 mm
Height	28 mm
Dimension a	120 mm
Dimension b	110 mm
Dimension h	28 mm

Technical data

Number of fixed partitions	2
Number of compartments	3 St.
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Trunking width, min.	350 mm
Duct height, min.	28 mm
Cross-section, draw a	2944 mm ²
Cross-section, draw b	2834 mm ²
ROHS-conformant	yes