


Technical data sheet

Trunking unit for GES9, height 65 mm

Item number: 7402224



3 compartment flush floor trunking with 3 mounting lids for GES9. Trunking unit consists of trunking connectors, fixing brackets and separating retainers.



St	Steel
FS	Strip galvanised

Master data

Item number	7402224
Type	OKA-T 30065 D9
Description 1	Flushfloor trunking unit
Description 2	for GES9
Manufacturer	OBO
Dimension	2400x300x65
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	2531.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	133,2858 kg CO2e / 1 Piece


Technical data sheet

Trunking unit for GES9, height 65 mm

Item number: 7402224



Dimensions



Length	2,400 mm
Width	300 mm
Height	65 mm
Dimension b	300 mm
Dimension h	65 mm

Technical data

Number of mounting openings	3
Number of planned flush-mount units	3
Number of compartments	3 St.
Expansion option	For installation of accessories
Cover fastening, locking	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Suitable for expansion joint	no
With separating retainer	yes
Mounting opening	For service outlet
Mounting opening	Square
Removable cover	yes
ROHS-conformant	Exempt
Heavy-duty version	no
Separating retainer fastening	rasten
Separating retainer fastening	Lock