

Technical data sheet

GES9/10 service trunking for OKA-T, 3-compartment

Item number: 7402290



Square flushfloor installation unit for mounting in an OKA-T trunking system. With mounting support to accept up to three APMT5 cover plates.
Service outlet with handle clamp for mounting in a OKA-T trunking system. With mounting support for receiving up to three APMT5 cover plates.



PA Polyamide

Master data

Item number	7402290
Type	GES9 10OK U 7011
Description 1	Service outlet
Description 2	with univ. mounting for OKA/T
Manufacturer	OBO
Dimension	264x264x67
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	211 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	5,7547 kg CO2e / 1 Piece


Technical data sheet

GES9/10 service trunking for OKA-T, 3-compartment

Item number: 7402290



Dimensions



Technical data

Cable outlet version	Swivellable cord outlet
Seal installation option	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
ROHS-conformant	yes
Clamping range D, max.	36 mm
Clamping range D, min.	14 mm
Opening mechanism	Handle
Floor covering thickness	10 mm