

Technical data sheet

Drilling template for supply trunking

Item number: 7403881



Drilling template for the construction-side creation of all the necessary holes for the mounting of a trunking unit, cut to length, without a brush bar.



St	Steel
FS	Strip galvanised

Master data

Item number	7403881
Type	OKB BS E
Description 1	Drilling template
Description 2	for feeder duct
Manufacturer	OBO
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	82.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	2,2162 kg CO2e / 1 Piece


Technical data sheet

Drilling template for supply trunking

Item number: 7403881



Dimensions



Technical data

Mounting opening cover	no
Type of accessory	Miscellaneous
Floor plate	yes
Floor care	Dry
Cover fastening, locking	no
Seal installation option	no
Decouplable	yes
Suitable for expansion joint	no
Suitable for screed-flush closed underfloor ducts	no
Suitable for flushfloor, open underfloor trunking	yes
Suitable for screed-covered underfloor ducts	no
Minimum screed height	85
With connection opening	no
With equipotential bonding	no
With overhang	yes
Height-adjustment range, min.	0 mm
Removable cover	yes
ROHS-conformant	yes