

Technical data sheet

UTC4 FI with 2 protective contact sockets and FI/LS

Item number: 7404692



Ready-for-connection universal support Connect UTC4 for decentralised protection, equipped with FI/LS and sockets. With WIELAND plug connector system GST 18. Suitable for VL connection cables and for use in device installation units of nominal sizes R7, 9 and R9.

The ready-for-connection UTC4 FI universal support has 2 protective contact sockets protected with FI/LS. Internal wiring with 2.5 mm². Please note the connection requirements (and also the selectivity).

Input side: Self-locking plug connector, 3-pin, type Wieland GST18 (connector)
Output side: Self-locking plug connector, 3-pin, type Wieland GST18 (socket)

Technical features FI/LS 1P+N:

Rated current AC 16 A

Measured voltage 230 V

Tripping characteristic B

Residual current type A (pulse and alternating current sensitive)

Sensitivity 30 mA

Nominal arresting capacity 10 kA



PA Polyamide

Master data

Item number	7404692
Type	UTC4 FI G WS2
Description 1	Universal support ConnectGST18
Description 2	with FI/LS, double white
Manufacturer	OBO
Dimension	208x45x85
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	76.1 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	2,342 kg CO2e / 1 Piece


Technical data sheet

UTC4 FI with 2 protective contact sockets and FI/LS


Item number: 7404692



Dimensions



Length	218 mm
Width	76 mm
Height	85 mm



Technical data

Number of connections	1
Number of installable devices	4
Number of strain reliefs	0
Version for	FI/LS/double pure white
Version for	Socket shape
Installation technology	Grid M45
Line cross-section	2.5 mm ²
Accessory mounting type	Lock
ROHS-conformant	Exempt
Socket combination	Double
Plug-in system	GST18
Plug connector system, system-specific	yes
Circuit	1
Surge protection	no
Number of cable entries	2