

Technical data sheet

On-floor installation trunking, trunking height 70 mm

Item number: 7404708



On-floor trunking base, 1 compartment, for blank/mounting lid with slope on one side, with plug-fit aluminium side profiles for layering and fixing the trunking lid, metal floor base with holding shackles for max. two plug-in, self-contacting dividers and groove for earth conductor clamp. Trunking height suitable for installation of service outlets of nominal size 2.



St

Steel

FS

Strip galvanised

Master data

Item number	7404708
Type	AIKU 20070
Description 1	Trunking base
Manufacturer	OBO
Dimension	2400x200x70
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	320.8 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	15,5625 kg CO2e / 1 Meter


Technical data sheet

On-floor installation trunking, trunking height 70 mm

Item number: 7404708



Dimensions



Length	2,400 mm
Width	200 mm
Height	70 mm
Plate thickness, base	1 mm
Dimension B	200 mm
Dimension b	200 mm
Dimension h	40 mm

Technical data

Number of insertable partitions	2
Number of compartments	3 St.
Suitable for	Cover sloping on one side
With separating retainer	no
Usable cross-section	132 cm ²
Cross-section, draw 3	5167 mm ²
Cross-section, draw a	5945 mm ²
Cross-section, draw b	2090 mm ²
ROHS-conformant	yes
Separating retainer fastening	stecken
Separating retainer fastening	Plug