

Technical data sheet

On-floor installation trunking, trunking height 75 mm

Item number: 7404720



On-floor trunking base, 1 compartment, for blank/mounting lid with slope on one side, with plug-fit aluminium side profiles for layering and fixing the trunking lid, metal floor base with holding shackles for max. two plug-in, self-contacting dividers and groove for earth conductor clamp. Trunking height suitable for installation of Telitanks or service outlets of nominal size 4, 6, 9.



St

Steel

FS

Strip galvanised

Master data

Item number	7404720
Type	AIKU 35075
Description 1	Trunking base
Manufacturer	OBO
Dimension	2400x375x75
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	445.2 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	18,249 kg CO2e / 1 Meter


Technical data sheet

On-floor installation trunking, trunking height 75 mm

Item number: 7404720



Dimensions



Length	2,400 mm
Width	350 mm
Height	75 mm
Plate thickness, base	1 mm
Dimension B	350 mm
Dimension b	350 mm
Dimension h	75 mm

Technical data

Number of insertable partitions	2
Number of compartments	3 St.
Suitable for	Cover sloping on one side
With separating retainer	no
Usable cross-section	248 cm ²
Cross-section, draw 3	10908 mm ²
Cross-section, draw a	11673 mm ²
Cross-section, draw b	2250 mm ²
ROHS-conformant	yes
Separating retainer fastening	stecken
Separating retainer fastening	Plug