

Technical data sheet

On-floor branch trunking

Item number: 7404874



On-floor junction trunking base for blank/mounting lid with slope on both sides, free on floor for mounting, with plug-fit aluminium side profiles for layering and fixing the trunking lid. Trunking height suitable for installation of Telitanks.



St

Steel

FS

Strip galvanised

Master data

Item number	7404874
Type	AIKA U 15040
Description 1	Junction trunking base
Description 2	for onfloor trunking
Manufacturer	OBO
Dimension	2400x150x40
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	223.1 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	10,9303 kg CO2e / 1 Meter


Technical data sheet

On-floor branch trunking

Item number: 7404874



Dimensions



Length	2,400 mm
Width	150 mm
Height	40 mm
Plate thickness, base	1 mm
Dimension B	150 mm
Dimension b	150 mm
Dimension h	40 mm

Technical data

Number of insertable partitions	2
Number of compartments	3 St.
Suitable for	Cover sloping on both sides
With separating retainer	no
Usable cross-section	45 cm ²
Cross-section, draw 3	1171 mm ²
Cross-section, draw a	1630 mm ²
Cross-section, draw b	1120 mm ²
ROHS-conformant	yes
Separating retainer fastening	stecken
Separating retainer fastening	Plug