

Technical data sheet

On-floor branch trunking

Item number: 7404882



Onfloor junction trunking base for blank/mounting lid with slope on both sides, free on floor for mounting, with plug-fit aluminium side profiles for layering and fixing the trunking lid. Trunking height suitable for installation of Telitanks.




St Steel

FS Strip galvanised

Master data

Item number	7404882
Type	AIKA U 25040
Description 1	Junction trunking base
Description 2	for onfloor trunking
Manufacturer	OBO
Dimension	2400x250x40
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	301.7 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	15,2813 kg CO2e / 1 Meter

Dimensions



Length	2,400 mm
Width	250 mm
Height	40 mm
Plate thickness, base	1 mm
Dimension B	250 mm
Dimension b	250 mm
Dimension h	40 mm

Technical data sheet

On-floor branch trunking

Item number: 7404882



Technical data

Number of insertable partitions	2
Number of compartments	3 St.
Suitable for	Cover sloping on both sides
With separating retainer	no
Usable cross-section	81 cm ²
Cross-section, draw 3	3571 mm ²
Cross-section, draw a	3430 mm ²
Cross-section, draw b	1120 mm ²
ROHS-conformant	yes
Separating retainer fastening	stecken
Separating retainer fastening	Plug