

Technical data sheet

Service outlet, square, for screed height 55 mm

Item number: 7405039



GES9 service outlet with a fixed construction height of 55 mm for use in installation trunking systems in dry rooms with dry-care floors in interior areas. With two installation housings for vertical mounting of Modul 45 devices and four strain reliefs. Two installation frames are required to mount Modul 45 devices.

The data modules are mounted using a maximum of two optional MPMT45 mounting plates.

The service outlet is equipped with universal fastening brackets.



PA Polyamide

Master data

Item number	7405039
Type	GES9 55U V 9011
Description 1	Service outlet
Description 2	for duct mounting
Manufacturer	OBO
Dimension	263x263x59
Colour	Graphite black; RAL 9011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	206.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	6,3663 kg CO2e / 1 Piece



Technical data sheet

Service outlet, square, for screed height 55 mm

Item number: 7405039



Dimensions



Length	263 mm
Width	263 mm
Height	59 mm
Dimension h	55 mm

Technical data

Number of installable devices	8
Cover version	Square
Cable outlet version	Swivellable cord outlet
Floor covering protection frame	yes
Floor care	Dry
Seal installation option	no
Screed height, min.	55 mm
Floor height, min.	58 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	yes
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	yes
Device support to accept mounting boxes	no
Length of external dimensions	263 mm
Length of installation dimensions	242 mm
With floor covering recess	no
Nominal size for device installation units	9
Frame version	Carpet protection frame
ROHS-conformant	yes
Heavy-duty version	no
Clamping range D, max.	31 mm
Clamping range D, min.	9 mm
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Opening mechanism	Handle
Floor covering thickness	5 mm