

Technical data sheet

GES9-3 service outlet with handle clamp, for 3 cover plates APMT5

Item number: 7405097



Service outlet with metal installation frame for mounting of 3 cover plates of shape APMT5, for use in UGD and UDS underfloor boxes.

Universal fastening brackets adjustable to floor thicknesses up to 65 mm.

Carpet protection frame, hinged lid and cord outlet made of PC/ABS.
Floor covering recess in the hinged cover pre-adjusted to 5 mm, if necessary adjustable to 10 mm.



PA Polyamide

Master data

Item number	7405097
Type	GES9-3 UME 7011
Description 1	Service outlet
Description 2	for UDS mounting
Manufacturer	OBO
Dimension	264x264x70
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	240 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	7,6241 kg CO2e / 1 Piece


Technical data sheet

GES9-3 service outlet with handle clamp, for 3 cover plates
APMT5

Item number: 7405097



Dimensions



Length	264 mm
Width	264 mm
Height	70 mm

Technical data

Number of installable devices	6
Number of mounting boxes	3
Cover version	Square
Cable outlet version	Swivellable cord outlet
Floor care	Dry
Seal installation option	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for wet care	no
Length of installation dimensions	244 mm
Frame version	Carpet protection frame
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK08
Clamping range D, max.	76 mm
Clamping range D, min.	8 mm
Opening mechanism	Handle
Floor covering thickness	5 mm
Floor covering thickness max.	10 mm