

Technical data sheet


GES6 service outlet with handle clamp

Item number: 7405316



Service outlet with handle clamp for up to 9 individual Modul 45 devices in three UT3 universal supports, use in trunking systems and system floors for indoor use.

Separate fastening brackets must be ordered for raised floor mounting.
Up to 6 installation devices with 50 mm central plate can be inserted.
Service outlet with handle clamp, 3-compartment, for the installation of MT6 mounting support. Three type APMT2 cover plates can be installed.



PA Polyamide

Master data

Item number	7405316
Type	GES6 U 1019
Description 1	Service outlet
Description 2	for duct mounting
Manufacturer	OBO
Dimension	273x220x61
Colour	Grey-beige; RAL 1019
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	150 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,8182 kg CO2e / 1 Piece


Technical data sheet

GES6 service outlet with handle clamp

Item number: 7405316



Dimensions



Length	220 mm
Width	273 mm

Technical data

Number of installable devices	9
Number of mounting boxes	3
Cover version	Rectangular
Cable outlet version	Swivellable cord outlet
Floor covering protection frame	yes
Floor care	Dry
Seal installation option	no
Floor height, min.	73 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor box	250/350
Suitable for underfloor ducts	yes
Device support to accept mounting boxes	yes
Length of external dimensions	220 mm
Length of installation dimensions	199 mm
With floor covering recess	yes
Nominal size for device installation units	6
Frame version	Carpet protection frame
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20

Technical data sheet

GES6 service outlet with handle clamp

Item number: 7405316



Technical data

Protection rating (IP) when unused	IP40
Protection rating IK code	IK08
Heavy-duty version	no
Clamping range D, max.	31 mm
Clamping range D, min.	9 mm
Installation system type	MT3 / GB2
Vertical load, large area	to 3,000 N
Vertical load, small area	to 2,500 N
Approvals	VDE
Opening mechanism	Handle
Floor covering thickness	5 mm