

Technical data sheet

Cover plate, 1.5x, for GESRM2

Item number: 7405427



Cover plate for GESRM2 to accept 1.5 Modul 45.



PA

Polyamide

Master data		
Item number	7405427	
Type	AP1.5 GESRM2	
Description 1	Cover plate	
Description 2	for GESRM2	
Manufacturer	OBO	
Dimension	72x85x14	
Colour	Graphite black; RAL 9011	
Material	Polyamide	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	1.46 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,1022 kg CO2e / 1 Piece	


Technical data sheet

Cover plate, 1.5x, for GESRM2


Item number: 7405427



Dimensions



Length	72 mm
Width	85 mm
Height	14 mm



Technical data

Application	Mounting box
Number of CEE/Perilex openings	0
Number of triple openings	0
Number of installable devices	1.5
Number of single openings	1
Number of oval openings	0
Number of square openings	0
Number of round openings	0
Number of double openings	0
Fastening type	Lockable
Labelling panel	no
Blanking lid	no
Seal installation option	no
Suitable for labelling panel	no
Device type	Miscellaneous
Installation technology	Grid M45
ROHS-conformant	yes
Strain relief option	yes