


Technical data sheet

Frame cassette for cord outlet, RKS, nominal size 250-3,
stainless steel

Item number: 7406550



Frame cassette for cord outlet, for UZD250-3, for the installation of accessories
in dry or wet-cleaned floors for indoor use.



A2


A4

Stainless steel Stainless steel

Master data

Item number	7406550
Type	RKS 2V2 15
Description 1	Frame cassette
Description 2	for cord outlet
Manufacturer	OBO
Dimension	282x282x15
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	402.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	18,5961 kg CO2e / 1 Piece

Dimensions



Dimension A	324 mm
Dimension B	288 mm
Dimension C	282 mm
Dimension h	15 mm

Technical data sheet

Frame cassette for cord outlet, RKS, nominal size 250-3,
stainless steel

Item number: 7406550



Technical data

Number of cable outlets	1
Cable outlet version	Swivellable cord outlet
Floor care	Dry
Suitable for	Underfloor socket structure
Suitable for underfloor box	250
Device support to accept mounting boxes	no
ROHS-conformant	yes
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Vertical load, large area	to 3,000 N
Vertical load, small area	to 3,000 N
Floor covering thickness	13 mm