


# Technical data sheet

## ZESR4 inspection cover

Item number: 7406776



Draw box insert for blanking locking of a square round mounting opening of nominal size R4 in trunking systems and system floors for indoor use.



PA Polyamide

| Master data                        |                          |
|------------------------------------|--------------------------|
| Item number                        | 7406776                  |
| Type                               | ZESR4 U 9011             |
| Description 1                      | Junction box insert      |
| Description 2                      | for universal mounting   |
| Manufacturer                       | OBO                      |
| Dimension                          | Ø234x33                  |
| Colour                             | Graphite black; RAL 9011 |
| Material                           | Polyamide                |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 140 kg                   |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 5,008 kg CO2e / 1 Piece  |


# Technical data sheet

## ZESR4 inspection cover

Item number: 7406776



### Dimensions



|        |        |
|--------|--------|
| Length | 234 mm |
| Width  | 234 mm |
| Height | 36 mm  |

### Technical data

|                                              |                         |
|----------------------------------------------|-------------------------|
| Cover version                                | Round                   |
| Floor care                                   | Dry                     |
| Floor height, min.                           | 60 mm                   |
| Suitable for raised floor installation       | yes                     |
| Suitable for screed-covered underfloor ducts | yes                     |
| Suitable for cavity floor installation       | yes                     |
| Suitable for wet care                        | no                      |
| Suitable for underfloor box                  | 250/350                 |
| Suitable for underfloor ducts                | yes                     |
| Nominal size for device installation units   | R4                      |
| Frame version                                | Carpet protection frame |
| ROHS-conformant                              | Exempt                  |
| Clamping range D, max.                       | 32 mm                   |
| Clamping range D, min.                       | 12 mm                   |
| Vertical load, large area                    | to 5,000 N              |
| Vertical load, small area                    | to 3,000 N              |
| Floor covering thickness                     | 5 mm                    |