

# Technical data sheet

Mounting support for data technology connection sockets,  
system length 165 mm

Item number: 7407677



Mounting support to accept two support plates. Use instead of a UT3 universal support.



**PA** Polyamide

## Master data

|                                    |                              |
|------------------------------------|------------------------------|
| Item number                        | 7407677                      |
| Type                               | MTK2                         |
| Description 1                      | Mounting support             |
| Description 2                      | for communication technology |
| Manufacturer                       | OBO                          |
| Dimension                          | 165x76x25                    |
| Colour                             | Graphite black; RAL 9011     |
| Material                           | Polyamide                    |
| Smallest sales unit                | 1                            |
| Unit of quantity                   | Piece                        |
| Weight                             | 4.523 kg                     |
| Weight unit                        | kg/100 pc.                   |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,2053 kg CO2e / 1 Piece     |


# Technical data sheet

Mounting support for data technology connection sockets,  
system length 165 mm

Item number: 7407677



## Dimensions



|        |        |
|--------|--------|
| Length | 165 mm |
| Width  | 76 mm  |
| Height | 25 mm  |

## Technical data

|                                                   |                                                             |
|---------------------------------------------------|-------------------------------------------------------------|
| Connection options                                | 2 support plates for data and multimedia connection modules |
| Version for                                       | Support shape                                               |
| Floor plate                                       | no                                                          |
| Seal installation option                          | no                                                          |
| Installation opening for on-floor tank            | no                                                          |
| Decouplable                                       | no                                                          |
| Suitable for raised floor installation            | yes                                                         |
| Suitable for screed-flush closed underfloor ducts | yes                                                         |
| Suitable for screed-covered underfloor ducts      | yes                                                         |
| Suitable for cavity floor installation            | yes                                                         |
| Suitable for underfloor ducts                     | yes                                                         |
| Accessory mounting type                           | Bolts                                                       |
| ROHS-conformant                                   | yes                                                         |
| Heavy-duty version                                | no                                                          |