

Technical data sheet

Mounting support, 2 x type B

Item number: 7407847



Mounting support to accept two data connection modules of the following types
BTR: E-DAT; Dätwyler: MS and MS-N; Kerpen: VarioKeystone.
Dimensions of a mounting opening in mm: 19.35/21.55 x 14.85.
Suitable for GE2 installation unit without floor covering recess.



A2 Stainless steel

Master data		
Item number	7407847	
Type	MTGE2 2B	
Description 1	Mounting plate	
Description 2	with 2x hole pattern Type B	
Manufacturer	OBO	
Dimension	116x36x34	
Material	Stainless steel 1.4301	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	3.3 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,5197 kg CO2e / 1 Piece	



Technical data sheet

Mounting support, 2 x type B

Item number: 7407847



Dimensions



Length	116 mm
--------	--------

Technical data

Number of installable devices	2
Number of strain reliefs	0
Version for	Support shape
Fastening type	Lockable
Labelling panel	no
Floor covering protection frame	no
Floor plate	no
Lowerable to be flush-floor	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	yes
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for underfloor ducts	yes
With floor covering recess	no
ROHS-conformant	yes
Heavy-duty version	no
Depth	36 mm
Strain relief option	yes