


Technical data sheet

Mounting plate 2 x data socket type C for System 55

Item number: 7408705



Mounting plate to accept two connection sockets for data technology of the following types: Brand-Rex: shielded module; EKU: E-Stone module; Dätwyler: KS-T, MS-K and KU-T module; R&M: Snap-In and Keystone module; Rutenbeck: UM and UMflex module; SETEC: MKJ, UKJ and XKJ module; Siemon TERA; Telegärtner: AMJ and UMJ module.
Dimensions of a mounting opening in mm: 19.30 x 14.80.



A2 Stainless steel

Master data

Item number	7408705
Type	MPMT45 2C
Description 1	Mounting plate
Description 2	with 2x hole pattern Type C
Manufacturer	OBO
Dimension	77x24x1,5
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	1.44 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1647 kg CO2e / 1 Piece


Technical data sheet

Mounting plate 2 x data socket type C for System 55

Item number: 7408705



Dimensions



Technical data

Connection options	2 connection sockets for data technology of the following types: Brand-Rex; EKU; Dätwyler; Rutenbeck; SETEC; Siemon TERA; Telegärtner
Fastening type	Lockable
Labelling panel	no
Floor covering protection frame	no
Floor plate	no
Lowerable to be flush-floor	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	yes
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for underfloor ducts	yes
With floor covering recess	no
ROHS-conformant	yes
Heavy-duty version	no
Strain relief option	yes