

# Technical data sheet

## Height-adjustable cassette for inspection opening, RKR, stainless steel

Item number: 7409128



Height-adjustable "blank" cassette for the creation of an inspection opening of nominal size R9 in dry or wet-cleaned floors for indoor use. Only suitable for smooth floor coverings.

Height-adjustable cassette as a blind cassette, 3-compartment. 3 APMT5 cover plates can be installed. For the installation of 3 UT4 universal supports for 9 individual installation devices with support ring/support clamp or 12 Modul 45 devices.

Height-adjustable cassette as a blanking cassette, 3-compartment.



A2 Stainless steel

### Master data

|                                    |                           |
|------------------------------------|---------------------------|
| Item number                        | 7409128                   |
| Type                               | RKRN2 R9 VS20             |
| Description 1                      | Round cassette            |
| Description 2                      | blank                     |
| Manufacturer                       | OBO                       |
| Dimension                          | Ø305mm                    |
| Material                           | Stainless steel 1.4301    |
| Smallest sales unit                | 1                         |
| Unit of quantity                   | Piece                     |
| Weight                             | 453 kg                    |
| Weight unit                        | kg/100 pc.                |
| CO2 Footprint (GWP) Cradle-to-Gate | 17,6663 kg CO2e / 1 Piece |


# Technical data sheet

Height-adjustable cassette for inspection opening, RKR,  
stainless steel

Item number: 7409128



## Dimensions



|        |        |
|--------|--------|
| Length | 304 mm |
| Width  | 304 mm |

## Technical data

|                                            |                 |
|--------------------------------------------|-----------------|
| Number of installable devices              | 0               |
| Number of mounting boxes                   | 3               |
| Number of cable outlets                    | 0               |
| Cover version                              | Round           |
| Cable outlet version                       | No cable outlet |
| Floor care                                 | Wet             |
| Decouplable                                | no              |
| Floor height, max.                         | 155 mm          |
| Floor height, min.                         | 105 mm          |
| Suitable for raised floor installation     | yes             |
| Suitable for cavity floor installation     | yes             |
| Suitable for underfloor box                | 350             |
| Device support to accept mounting boxes    | no              |
| Nominal size for device installation units | R9              |
| Height-adjustment range, max.              | 155 mm          |
| Height-adjustment range, min.              | 105 mm          |
| ROHS-conformant                            | Exempt          |
| Protection rating (IP) when used           | IP00            |
| Protection rating (IP) when unused         | IP44            |
| Protection rating IK code                  | IK10            |
| Heavy-duty version                         | no              |
| Installation system type                   | UT4             |
| Vertical load, large area                  | to 5,000 N      |
| Vertical load, small area                  | to 3,000 N      |
| Approvals                                  | VDE             |
| Floor covering thickness                   | 20 mm           |