

Technical data sheet

Height-adjustable cassette with cord outlet, RКСN, brass

Item number: 7409204



Height-adjustable cassette of nominal size 4 with cord outlet for installation of accessories in dry-care floors for indoor use.
Height-adjustable cassette for cord outlet, 2-compartment. 2 APMT2 cover plates can be installed. For the installation of 2 UT3 universal supports for 4 individual installation devices with support ring/support clamp or 6 Modul 45 devices.



CuZn
37 Brass

Master data

Item number	7409204
Type	RКСN2 4 MS 25
Description 1	Square cassette
Description 2	with cord outlet
Manufacturer	OBO
Dimension	200x200mm
Material	Brass
Smallest sales unit	1
Unit of quantity	Piece
Weight	328 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	11,5475 kg CO2e / 1 Piece


Technical data sheet

Height-adjustable cassette with cord outlet, RКСN, brass

Item number: 7409204



Dimensions



Dimension h 110 mm

Technical data

Number of installable devices	6
Number of mounting boxes	2
Number of cable outlets	1
Cover version	Square
Cable outlet version	Swivellable cord outlet
Floor care	Dry
Decouplable	no
Floor height, max.	155 mm
Floor height, min.	110 mm
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for underfloor box	250/350
Device support to accept mounting boxes	yes
Length of installation dimensions	201 mm
Nominal size for device installation units	4
Height-adjustment range, max.	155 mm
Height-adjustment range, min.	110 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no
Installation system type	UT3
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE
Floor covering thickness	25 mm