


Technical data sheet

Height-adjustable cassette with cord outlet, RКСN, stainless steel

Item number: 7409218



Height-adjustable cassette of nominal size 9 with cord outlet for installation of accessories in dry-care floors for indoor use .
For the installation of 3 UT4 universal supports for 9 individual installation devices with support ring/support clamp or 12 Modul 45® devices.
Height-adjustable square cassette, 3-compartment, with cord outlet of nominal size 9 for the installation of accessories. Cassette suitable for the use in trunking systems, raised and cavity floors in dry- and wet-cleaned floors in indoor areas. Suitable only for smooth floor coverings. Three cover plates APMT5 can be installed.



A2 Stainless steel

Master data

Item number	7409218
Type	RКСN2 9 VS 20
Description 1	Square cassette
Description 2	with cord outlet
Manufacturer	OBO
Dimension	243x243mm
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	430 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	20,7553 kg CO2e / 1 Piece


Technical data sheet

Height-adjustable cassette with cord outlet, RКСN, stainless steel

Item number: 7409218



Dimensions



Length	243 mm
Width	243 mm
Dimension h	105 mm

Technical data

Number of installable devices	12
Number of mounting boxes	3
Number of cable outlets	1
Cover version	Square
Cable outlet version	Swivellable cord outlet
Floor care	Dry
Decouplable	no
Floor height, max.	150 mm
Floor height, min.	105 mm
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for	Underfloor socket structure
Suitable for underfloor box	250/350
Device support to accept mounting boxes	yes
Length of installation dimensions	244 mm
Nominal size	350 mm
Nominal size for device installation units	9
Height-adjustment range, max.	150 mm
Height-adjustment range, min.	105 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no
Installation system type	UT4
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE

Technical data sheet

Height-adjustable cassette with cord outlet, RКСN, stainless steel

Item number: 7409218



Technical data

Floor covering thickness	20 mm
--------------------------	-------