

# Technical data sheet

Frame cassette for tube body, RKF, nominal size 250-3,  
stainless steel

Item number: 7409410



Frame cassette for tube body, for UZD250-3, for the installation of accessories in dry or wet-cleaned floors in interior areas. The tube body is not contained in the scope of delivery.



A2 Stainless steel

## Master data

|                                    |                           |
|------------------------------------|---------------------------|
| Item number                        | 7409410                   |
| Type                               | RKF3 V2 30                |
| Description 1                      | Frame cassette            |
| Description 2                      | for tube                  |
| Manufacturer                       | OBO                       |
| Dimension                          | 283x283x30                |
| Material                           | Stainless steel 1.4301    |
| Smallest sales unit                | 1                         |
| Unit of quantity                   | Piece                     |
| Weight                             | 476.9 kg                  |
| Weight unit                        | kg/100 pc.                |
| CO2 Footprint (GWP) Cradle-to-Gate | 21,0109 kg CO2e / 1 Piece |


# Technical data sheet

Frame cassette for tube body, RKF, nominal size 250-3,  
stainless steel

Item number: 7409410



## Dimensions



|             |        |
|-------------|--------|
| Dimension A | 324 mm |
| Dimension B | 288 mm |
| Dimension C | 282 mm |
| Dimension h | 30 mm  |

## Technical data

|                                         |                             |
|-----------------------------------------|-----------------------------|
| Number of cable outlets                 | 1                           |
| Cable outlet version                    | Lowerable tube body         |
| Floor care                              | Wet                         |
| Suitable for                            | Underfloor socket structure |
| Suitable for underfloor box             | 250                         |
| Device support to accept mounting boxes | no                          |
| ROHS-conformant                         | yes                         |
| Protection rating (IP) when used        | IP20                        |
| Protection rating (IP) when unused      | IP44                        |
| Vertical load, large area               | to 3,000 N                  |
| Vertical load, small area               | to 3,000 N                  |
| Floor covering thickness                | 28 mm                       |