

# Technical data sheet

Height-adjustable heavy-duty cassette for tube body RK-FRSL, nominal size R9, stainless steel  
Item number: 7409472



Round heavy-duty cassette for tube body of nominal size R9 for the installation of accessories in trunking systems, raised and cavity floors, in dry or wet-cleaned floors. Load class 2 to 20 kN.

Height-adjustable heavy-duty cassette with tube body with a load bearing capacity of 2-20 kN, 3-compartment. 3 APMT5 cover plates can be installed. For the installation of three UT4 universal supports for nine single accessories with support ring/support clamp or 12 Modul 45 devices. The tube body is not contained in the scope of delivery.

Height-adjustable round cassette, 3-compartment, of nominal size 9, for tube bodies. For the installation in trunking systems and in raised and cavity floors in dry- or wet-cleaned floors in indoor areas. Load class 2 to 20 kN. Three cover plates APMT5 can be installed.



A2 Stainless steel

## Master data


|                                    |                           |
|------------------------------------|---------------------------|
| Item number                        | 7409472                   |
| Type                               | RKFR2 9 SL2V2 25          |
| Description 1                      | Heavy-duty cassette       |
| Description 2                      | for tube, 20 kN           |
| Manufacturer                       | OBO                       |
| Dimension                          | Ø305mm                    |
| Material                           | Stainless steel 1.4301    |
| Smallest sales unit                | 1                         |
| Unit of quantity                   | Piece                     |
| Weight                             | 647 kg                    |
| Weight unit                        | kg/100 pc.                |
| CO2 Footprint (GWP) Cradle-to-Gate | 25,7308 kg CO2e / 1 Piece |

# Technical data sheet

Height-adjustable heavy-duty cassette for tube body RK-FRSL, nominal size R9, stainless steel  
Item number: 7409472



## Dimensions



|             |        |
|-------------|--------|
| Dimension h | 114 mm |
|-------------|--------|

## Technical data

|                                            |                     |
|--------------------------------------------|---------------------|
| Number of installable devices              | 12                  |
| Number of mounting boxes                   | 3                   |
| Number of cable outlets                    | 1                   |
| Cover version                              | Round               |
| Cable outlet version                       | Lowerable tube body |
| Floor care                                 | Wet                 |
| Decouplable                                | no                  |
| Floor height, max.                         | 159 mm              |
| Floor height, min.                         | 114 mm              |
| Suitable for raised floor installation     | yes                 |
| Suitable for cavity floor installation     | yes                 |
| Suitable for underfloor box                | 350                 |
| Device support to accept mounting boxes    | yes                 |
| Nominal size for device installation units | R9                  |
| Height-adjustment range, max.              | 159 mm              |
| Height-adjustment range, min.              | 114 mm              |
| Protection rating (IP) when used           | IP20                |
| Protection rating (IP) when unused         | IP44                |
| Protection rating IK code                  | IK10                |
| Heavy-duty version                         | yes                 |
| Heavy load class                           | 20 kN (OBO SL2)     |
| Installation system type                   | UT4                 |
| Floor covering thickness                   | 25 mm               |