

Technical data sheet

Threaded rod for UZD 250/350

Item number: 7410017



Threaded rod as spare part for height adjustment of the UZD 250/350.



PA/
GF

Polyamide, fibreglass reinforced

Master data

Item number	7410017
Type	UZD GS 250/350
Description 1	Threaded rod
Description 2	for UZD
Manufacturer	OBO
Dimension	140x140x25
Colour	Pastel orange; RAL 2003
Material	Polyamide, fibreglass reinforced
Smallest sales unit	1
Unit of quantity	Packaging unit
Weight	7.5 kg
Weight unit	kg/100 PUs
CO2 Footprint (GWP) Cradle-to-Gate	0,3238 kg CO2e / 8 Piece

Technical data sheet

Threaded rod for UZD 250/350

Item number: 7410017



Dimensions



Length	47.5 mm
Dimension d Ø	21.5 mm
Dimension h	47.5 mm

Technical data

Floor plate	no
Lowerable to be flush-floor	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Screed height, max.	320 mm
Screed height, min.	160 mm
For pipe connection	no
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Suitable for underfloor ducts	yes
Thread metric	22
Thread type	Metric
Thread pitches per inch	11
Thread increase	2.2 mm
Trunking width, max.	350 mm
Trunking width, min.	190 mm
Minimum screed height	160
Height-adjustment range, max.	320 mm
Height-adjustment range, min.	160 mm
ROHS-conformant	yes
Left thread	no