

Technical data sheet

Height-compensation kit ASH 350-4 240

Item number: 7410138



Height-compensation kit for UZD350-4 underfloor boxes with a construction height of 160 to 240 mm for construction-side raising of the UZD.



St	Steel
FS	Strip galvanised

Master data

Item number	7410138
Type	ASH 350-4 240
Description 1	Height compensation set
Description 2	for UZD 350-4
Manufacturer	OBO
Dimension	450x103x46
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Packaging unit
Weight	115 kg
Weight unit	kg/100 PUs
CO2 Footprint (GWP) Cradle-to-Gate	3,3837 kg CO2e / 4 Piece

Technical data sheet

Height-compensation kit ASH 350-4 240

Item number: 7410138



Dimensions



Length	450 mm
Width	103 mm
Dimension A	450 mm
Dimension B	103 mm
Dimension I	47.5 mm

Technical data

Version for	Square
Floor plate	no
Lowerable to be flush-floor	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Screed height, max.	240 mm
Screed height, min.	160 mm
For pipe connection	no
Suitable for raised floor installation	no
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	no
Suitable for underfloor ducts	no
Trunking width, max.	350 mm
Trunking width, min.	190 mm
Minimum screed height	160
Height-adjustment range, max.	240 mm
Height-adjustment range, min.	160 mm
ROHS-conformant	yes